

JASPER SOFA/SOFA BED

Product Data Sheet
Latest update: 3/03/2026

**SOFT
LINE**



Art. No.: 2-550

Design by Busk+Hertzog, 2011

Stylish and practical The modern sofa JASPER has a contemporary design, ideal for both private homes and public spaces. The backrest design lets you sit in the "corners" of the sofa, offering many more ways to relax than the average sofa bed. As an extra hidden feature JASPER is easily converted into a comfortable bed for two adults.

Functionality

The back rest design is both dynamic and practical as it lets you sit in the corners.

It can be used as a comfortable single bed and can be easily converted into a guest bed for two persons.

The sofa is elegant from all sides and can be placed freely in the room as a room divider.

It is constructed so it is easy to place / fasten the sheet when the bed is used as a single or doublebed.

The two cushions are loose and can be placed after individual needs.

A removable cover for cleaning and changing.

A multifunctional piece of furniture that can be used in the living room, guest room, summer cottage, holiday apartment, dormitory room, hotel, reception etc.

Design Vision

Dynamic and practical.

Design allows many comfortable sitting and lounging positions.

Easily converted into a single or doublebed.

Elegant from all sides – can be used as a roomdivider.

A large selection of fabrics and colours.

High quality.

Modern timeless design.

Removable cover for cleaning and changing.

Possibility to buy new covers.

Dimensions (cm)

Art. no.:	2-550
Length:	212
Depth:	83
Height:	72
Seat height:	39
Seat depth:	55
Bed:	70/140X20

Materials

Upholstery

Seat:

Top: Cold cured foam 35 kg/m³ and 200 g polyesterfiber.

Lower mattress: High elastic PU-foam 30 kg/m³.

Arm- / back rest:

Cold cured foam 35 kg/m³ and 100 g polyesterfiber.

Back cushions:

Frame

Steel.

Legs

Steel, High gloss chromed and with black glides.

Feather filling. Fabric (inner cover): 100% Polycotton. Sort of filling: 100% Feathers. Filling/Weight: 2430 Gr. Polyurethane foam tested according to Øko-tex 100.

Care and Maintenance

Removable covers. Cleaning: If the symbol P is on the care label, the cover can be dry-cleaned. Extra covers can be purchased if you need a new colour or fabric. We recommend to vacuum the covers often. For further information, please find our Care and Maintenance guide, which includes advice and instructions on cleaning and caring to prolong the life of your SOFTLINE product.

[View Care and Maintenance guide](#) →

Downloads

Download high-res images, 3d files and more via the SOFTLINE Media Bank.

[Go to SOFTLINE Media Bank](#) →